


Number of contacts

6-64



SMC male header with straight solder pins, kinked

Identification	No. of contacts	Part No.					
		Without levers		With short levers		With long levers	

SMC male header with straight solder pins, kinked
Length: 2.9 mm

6	09 19 506	└ 024	09 19 506	└ 014	09 19 506	└ 004
10	09 19 510	└ 024	09 19 510	└ 014	09 19 510	└ 004
14	09 19 514	└ 024	09 19 514	└ 014	09 19 514	└ 004
16	09 19 516	└ 024	09 19 516	└ 014	09 19 516	└ 004
20	09 19 520	└ 024	09 19 520	└ 014	09 19 520	└ 004
24	09 19 524	└ 024	09 19 524	└ 014	09 19 524	└ 004
26	09 19 526	└ 024	09 19 526	└ 014	09 19 526	└ 004
30	09 19 530	└ 024	09 19 530	└ 014	09 19 530	└ 004
34	09 19 534	└ 024	09 19 534	└ 014	09 19 534	└ 004
40	09 19 540	└ 024	09 19 540	└ 014	09 19 540	└ 004
50	09 19 550	└ 024	09 19 550	└ 014	09 19 550	└ 004
60	09 19 560	└ 024	09 19 560	└ 014	09 19 560	└ 004
64	09 19 564	└ 024	09 19 564	└ 014	09 19 564	└ 004

SEK

* Not normally kept in stock
For accessories see page 08.52
For dimensions see page 08.47

For performance level 3 please specify digit
For performance level 2 please specify digit
S4 = 0.76 µm (30 µinch) Au or PdNi equivalent

