



8AWG 27/7 stranded, PUR	09 45 744 1534	20 m
8AWG 27/7 stranded, PUR	09 45 744 1533	15 m
8AWG 27/7 stranded, PUR	09 45 744 1532	10 m
8AWG 27/7 stranded, PUR	09 45 744 1531	9 m
8AWG 27/7 stranded, PUR	09 45 744 1530	8 m
8AWG 27/7 stranded, PUR	09 45 744 1529	7 m
8AWG 27/7 stranded, PUR	09 45 744 1528	6 m
8AWG 27/7 stranded, PUR	09 45 744 1527	5 m
8AWG 27/7 stranded, PUR	09 45 744 1526	4 m
8AWG 27/7 stranded, PUR	09 45 744 1525	3 m
8AWG 27/7 stranded, PUR	09 45 744 1524	2 m
8AWG 27/7 stranded, PUR	09 45 744 1523	1,5 m
8AWG 27/7 stranded, PUR	09 45 744 1522	1 m
8AWG 27/7 stranded, PUR	09 45 744 1521	0,5 m
8AWG 28/7 stranded, PVC	09 45 745 1553	20 m
8AWG 28/7 stranded, PVC	09 45 745 1552	15 m
8AWG 28/7 stranded, PVC	09 45 745 1551	10 m
8AWG 28/7 stranded, PVC	09 45 745 1532	0,25m
8AWG 28/7 stranded, PVC	09 45 745 1527	5 m
8AWG 28/7 stranded, PVC	09 45 745 1525	3 m
8AWG 28/7 stranded, PVC	09 45 745 1523	1,5 m
Type of cable	Part-No.	Dim. a

-Transmission properties in accordance with ISO/IEC 11801:2002: Class E.
 -Protection level: IP67/65
 -Temperature range: -40°C ...+70°C

All Dimensions in mm Original Size DIN A 3			Techn. Character.			Nicht tolerierte Maß/Free size tolerances			
Mod.	Dat.	Name	Detail.	Insp.	Stand.	Maßstab/Scale 2:1	RJ1 cord, 2xRJ45, IP67-Push Pull 8AWG, stranded, CAT6		
			08.10.07	MR				TB 09 45 74x xxxx	Blatt/ page
35600	17.02.09	MR							
35037	04.11.08	MS							
34108									
HARTING Electronics GmbH & Co. KG D-32339 ESPELKAMP			Sub.						

Alle Rechte vorbehalten/ All rights reserved

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09457441523](#) [09457441525](#) [09457441527](#) [09457441532](#) [09457441534](#)