






Identification	Part No.	Drawing	Dimensions in mm
Fibre optic cable, double ended, multi mode, metal, 50 µm 2 x Han® 3 A, 2 x LC duplex Length: a = 1 m a = 5 m a = 10 m a = 20 m a = 40 m a = 50 m a = 100 m	33 54 211 0010 002 33 54 211 0050 002 33 54 211 0100 002 33 54 211 0200 002 33 54 211 0400 002 33 54 211 0500 002 33 54 211 1000 002	double ended  a = length	
Fibre optic cable, single ended, multi mode, metal, 50 µm 1 x Han® 3 A, 2 x LC duplex Length: a = 1 m a = 5 m a = 10 m a = 20 m a = 40 m a = 50 m a = 100 m	33 54 111 0010 002 33 54 111 0050 002 33 54 111 0100 002 33 54 111 0200 002 33 54 111 0400 002 33 54 111 0500 002 33 54 111 1000 002	Protection level: IP 65 / IP 67 single ended  a = length	
Fibre optic breakout cable , multi mode, 50 µm Length: 10 m Length: 20 m Length: 100 m	33 54 751 0100 002 33 54 751 0200 002 33 54 751 1000 002	 FRNC jacket 4-fibre multi mode 50 µm Outer diameter: 7.9 mm Min. bending radius: Installation: 9.8 cm Operating: 7.9 cm	

Further cable lengths are available on request