



## 6.5" Open Frame

<b>Part No</b>	:	<b>HE065AOT4</b>
<b>Item Description</b>	:	<b>6.5" monitor / 4 wire resistive touch</b>

Advantage and Application
<ul style="list-style-type: none"> <li>■ long term availability of adopted TFT LCD panels (stability of supply for min. 3 years)</li> <li>■ Analog RGB / DVI supportable</li> <li>■ 4 wire resistive touch adopted</li> <li>■ RS232 communication (option)</li> <li>■ Fine finishing metal chassis (brilliant design &amp; complete set level OSD button)</li> <li>■ Application               <ul style="list-style-type: none"> <li>- Kiosks</li> <li>- ATMs</li> <li>- Casino &amp; Amusement games</li> <li>- Lottery and Ticket sales</li> <li>- Self-Services</li> <li>- Industrial process control</li> </ul> </li> </ul>

Item	Description
Frame / bezel Color	EGL in black
Display Type	Size: 6.5" diagonal, Type: Active matrix TFT LCD Aspect ratio: 4 x 3
Active area	132.48 (H) x 99.36 (V)
Optimal (native) resolution	640 x 480
Support color	16.2 M colors
Brightness (without touch)	700 cd/m2
Viewing Angles	80 / 80 / 70 / 70
Input video supportable	Analog RGB, DVI, Audio (option, 2W x 2W)
Temperature	Operating ; - 30°C ~ +85 °C Storage : - 30°C ~ +85 °C
Mounting Holes	VESA standard mounting 75 x 75 mm
Applicable Graphic Mode	VESA standard timing control
Weight & Volume	Unit Weight : 1,100 g Carton Packing : pcs Carton weight : Kg

