









SHAFT TRAVEL CHART



10 PIN BRAD-HARRISON
CONNECTOR DETAIL

- NOTES
- 1 - TWO CONDUIT THREAD PLUGS ARE INCLUDED WITH PRODUCT
 - 2 - NOMENCLATURE IS PROVIDED FOR IDENTIFICATION OF EXISTING LISTINGS.
NOT ALL COMBINATIONS ARE AVAILABLE
 - 3 - POSITIVE OPENING TO IEC/EN60947-5-1
 - 4 - FORCE TO MAINTAIN ACTUATION SHAFT AT PROPER TENSION: 25 LBS
ACTUATION SHAFT OPERATE FORCE: 40 LBS

ELECTRICAL RATING				ENVIRONMENTAL		APPROVALS	
AC		DC		IP 67 NEMA 1, 4, 12 & 13		 IEC/EN60947-5-5	
A300 Ue	AC15 Ie	Q300 Uc	DC13 Ic	TEMP RANGE: -25°C TO 85°C -13°F TO 185°F			
(VOLTS) 120 240	(AMPS) 6 3	(VOLTS) 24 125 250	(AMPS) 2.8 .55 .27	STORAGE: -40°C TO 85°C -40°F TO 185°F			
Ith = 10A				SHOCK: 15G PER IEC 68-2-27 VIBRATION: 3G PER IEC 68-2-28			

DESIGN UNITS: INCH	DRAWN	AS	09NOV04	Honeywell SWITCH, ASSEMBLY			
TOLERANCES UNLESS NOTED:	CHECK	AK	09NOV04				
NO PLACE X ± 0.040	THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE			
ONE PLACE .X ± 0.030							
TWO PLACE .XX ± 0.015							
THREE PLACE .XXX ± 0.005							
FOUR PLACE .XXXX ± 0.0005	INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME	
ANGLES X ± 3				D	I	ICPS SERIES CHART 3	
THIRD ANGLE PROJECTION				REV A			
				Prof/ENGINEER 3D SCALE 1:1			
				SHEET 1 OF 1			