




REV	DESCRIPTION	DET	DATE
D	ITEM 3, 130050 WAS 123188	EL	11/09/11
E	128509C WAS 128619C, ADDED 128487	JJC	07/31/12



NOTES:

- 1 MAXIMUM RECOMMENDED STROKE .500
- 2 FOR USE WITH THE 206-375 TOOL. FOR OTHER TOOLS AND/OR STROKE COMBINATIONS, REFER TO THE STROKE LIMITER CHART (HK1122) OR CONSULT AN AFS/HUCK SPECIALIST.
- 3 SHIP WITH: STOP 126747, DEFLECTOR 126748-3 AND (2) .030 SHIMS 128290 REFERENCE PB563 FOR PROPER USE.
- 4 128619C ASSEMBLY CONSISTS OF 128509C COLLET AND 128487 DRAWBAR.



128487	1	DRAWBAR	9
126748-3	1	UNITIZED DEFLECTOR	8
128509C	1	COLLET	7
126745	1	GUARD	6
120095	1	DEFLECTOR	5
122727-1	1	BARBED RETAINER	4
130050	1	UNITIZED CHUCK JAW	3
127582-1	1	TOP GUARD	2
127069C	1	ANVIL	1
PART NO.	QTY	DESCRIPTION	ITEM

IDENTIFICATION PER SPEC 42-311: ★ ETCH	HUCK INTERNATIONAL, INC., I.S.D 1 CORPORATE DR KINGSTON, NEW YORK 12401		
ITAR/ECCN: EAR99	CLEARANCE NOSER ASSEMBLY -05 GP STRADDLE, SHEAR		
SCH B#: 8467.99.0190	FINAL ASSY: -		
HTS: 8467.99.0190	ENG: MVM CK:	DATE: 10/15/04	SCALE: 2:1
B		99-3738SC	