

Twist-Lock® Devices

30 Ampere, 3Ø Y 120/208, 277/480 and 347/600 Volts AC

4 Pole, 5 Wire Grounding

Insulgrip® Connector Bodies and Receptacles

30A 3ØY
120/208V AC
NEMA L21-30R
UL/CSA
3 HP



30A 3ØY
277/480V AC
NEMA L22-30R
UL/CSA
10 HP



30A 3ØY
347/600V AC
NEMA L23-30R
UL/CSA
10 HP

Connector Bodies**Watertight Safety-Shroud®****IP66 SUITABILITY**

Description	Cord Dia.	Catalog Numbers
Black Valox® housing, white Valox® clamps.	.35"-1.15" (9-29)	HBL2813SW

**HBL2813SW****Insulgrip****IP20 SUITABILITY**

Description	Cord Dia.	Catalog Numbers
Black and white nylon.	.35"-1.15" (9-29)	HBL2813 HBL2823 HBL2833
Corrosion resistant, yellow nylon.	.35"-1.15" (9-29)	HBL28CM13
Black and white for flat cable.	.35"-1.15" (9-29)	HBL2813FC
All black nylon.	.35"-1.15" (9-29)	HBL2813BK

**HBL2813**

Accessories on page B-53.

Receptacles**Watertight Safety-Shroud, Back Wired****IP66 SUITABILITY**

Description	Catalog Numbers
Gray Valox® housing and flange.	HBL2810SW

Accessories on page B-54.

**HBL2810SW****Safety-Shroud Twist-Lock, Back Wired****IP20 SUITABILITY**

Description	Catalog Numbers
Gray Valox® angle housing, one gang.	HBL2810AR
Gray Valox® surface mounting, one gang.	HBL2810SR
Gray Valox® semi-flush, two gang.	HBL2810SR2

Accessories on page B-54.

Single Flush, Back and Side Wired**IP20 SUITABILITY**




Description	Catalog Numbers
Black nylon face.	HBL2810 HBL2820 HBL2830
Isolated ground, orange nylon face.	IG2810
Ring terminal connection.	HBL2810RT

Accessories on page B-52.

**HBL2810AR****Insulgrip Flanged Receptacles**

Description	Catalog Numbers
Nylon casing, back wired.	HBL2816 HBL2826 HBL2836

Accessories on page B-52.

**HBL2816****HBL2810****HBL2810SR2****HBL2810SR**

Valox® is a trademark of SABIC Innovative Plastics, acquired from General Electric Company.