



Features:

- N.A. AC input
- Fully enclosed plastic case
- Fully regulated output
- High Efficiency
- Warranty: 5 years

Environmental

- Operating temperature....0° C to 40° C
- Storage temperature.....-55° C to 85° C
- Weight: 0.5 lbs

EMI

Meets FCC class B

Safety

UL 1950
cUL Listed to CSA 22.2 No. 950

Electrical specifications

Input

- Voltage.....90-132VAC
- Current.....0.75A
- Frequency.....47-63 Hz
- Input connector.....2 Pin NEMA 5/15 plug

Output

- Line regulation.....TYP 1%
- Load regulation.....5% Max
- Set point..... 5% of rated output
- Hold up time.....12 ms min. at full load 115 V

- Over voltage protection.....Built-in
- Over current protection.....Built-in
- Short circuit protection.....Pulsing Mode, auto recovery
- Ripple/noise(Vp-p).....1%
- Output connector.....barrel type(5.5 x 2.5 x 9.5mm)



Output Electrical Specifications

Model No.	Voltage	Power	Current
WP1205-760	5	12	2.4A
WP1215-760	15	12	0.8A
WP1212-760	12	12	1A
WP1224-760	24	12	0.5A



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Elpac \(ICCNexergy\):](#)

[WP1224-760](#) [WP1212-760](#) [WP1205-760](#)