

Cables for Dragon6 and Oslon6 Strips

CAB-ILS-GD06-INPUT
 CAB-ILS-GD06-LINK

Product Overview

Connection cables for use with to ILS' Dragon6 and Oslon6 Strips
 Employs JST PH type connector
 Cable length 300 mm
 CAB-ILS-GD06-INPUT: Power Input
 CAB-ILS-GD06-LINK: Linking strips




Ratings etc:


Maximum current	2 amps
Temperature range	-25° to +85°C
Insulation resistance	1,000 m Ohms min
Withstanding voltage	800V AC/minute
RoHS compliant	Yes

*This datasheet should be read in conjunction with the relevant JST data on the connector used

Drawing:



CAB-ILS-GD06-INPUT



CAB-ILS-GD06-LINK

Important Information and Precautions

- Do not exceed the maximum current and voltage
- Minimum bend radius for cables is 5 mm
- Do not pull on cables or use them for physical support

The values contained in this data sheet can change due to technical innovations. Any such changes will be made without separate notification.