

ISO-TIP

A division of Senasys.

www.iso-tip.com
(715) 831-6353

BUTANE-POWERED Soldering Irons

SOLDER-PRO Series

The versatile Solder Pro Series of cordless soldering irons can also be adapted for use as a torch, hot knife, and heat tool. And, since they're powered by readily-available butane fuel, there's no electrical current to leak to sensitive circuits. They're compact, portable, and dependable under all types of weather conditions.



The Compact **SOLDER PRO 50**

MODEL 7971 includes soldering iron, #7992 1.mm conical tip, protective cap with igniter and instructions.

- Compact size - only 5.5" with tip (6" with cap)
- Up to 30 minute run time
- Soldering temperatures 410° F - 750° F



The Standard **SOLDER PRO 70**

MODEL 7974 includes soldering iron, #7992 1.mm conical tip, protective cap with igniter and instructions.

- Standard size - only 7.5" with tip (8.75" with cap)
- Up to 120 minute run time
- Soldering temperatures 410° F - 850° F



The Ultimate **SOLDER PRO 120**

MODEL 7974 includes soldering iron, #7992-005 1.6 mm conical tip, #7992-008 torch tip, protective cap and instructions.

- Automatic ignition
- Up to 200 minute run time
- Soldering temperatures 480° F - 1,000° F
- Torch temperature 2400° F

Tips to match any job.

SOLDER PRO 50 & 70



7992
1.mm
conical tip



7992-001
2.mm
chisel tip



7992-002
hot knife
tip



7992-003
torch
tip



7992-004
heat blower
& deflector



7992-005
1.6 mm
conical tip



7992-006
2.4 mm
chisel tip



7992-007
3.2 mm
chisel tip



7992-008
torch
tip



7992-009
hot knife
tip



7992-101
heat
blower