

# 95 36 280 Cable Cutter

ratchet action



- Technical details
- Description
- Applications

<b>No.</b>	95 36 280	
<b>EAN</b>	4003773026891	
<b>tool</b>	black lacquered	
<b>Handles</b>	insulated with multi-component grips, VDE-tested	
<b>Insulation standard</b>	IEC 60900 DIN EN 60900	
	52.00	Ø mm
	380.00	mm <sup>2</sup>
<b>MCM</b>	750	
	280	mm
	835	g

- for cutting copper and aluminium cables, single and multiple wire
- not suitable for steel wire and wire ropes
- precision ground, hardened blades
- clean and smooth cut without crushing and deformation
- one-hand operation using ratchet principle
- little handforce required due to very high transmission ratio
- two-stage ratchet drive for easy cutting
- simple handling as a result of low weight and compact design - can be used even in confined areas

- with guard
- High-grade special tool steel, forged, oil-hardened



Ratchet principle and two-stage ratchet drive for easier cutting

### Spare Parts

No.	EAN	
95 39 280	4003773025283	Movable spare blade for 95 31 280 / 95 36 280

technical change and errors excepted