


PLCC Sockets

151-1568, 151-1569



PLCC Sockets

151-1568, 151-1569



Dimensions: In.

| SPECIFICATIONS | |
|------------------------|---------------------------------|
| Type: | PLCC 68 pin, thru-hole |
| Contact resistance: | 30mΩ max. @ 100mA DC |
| Insulator resistance: | 1000MΩ min. @ 500VDC |
| Current rating: | 1 amp |
| Voltage rating: | 500VAC for 1 minute |
| Operating temperature: | -65°C to +125°C |
| Contact material: | plated phosphor bronze |
| Contact plating: | tin (151-1568); gold (151-1569) |
| Housing material: | PPS and 40% glass fiber |

Date Last Revised: 10-18-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300755

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[151-1569](#) [151-1568](#)