

D-Sub Connector PC Pins


152-5209-E, 152-5215-E, 152-5225-E, 152-5237-E,
152-5250-E, 152-5309-E, 152-5315-E, 152-5325-E,
152-5337-E, 152-5350-E

KOBICONN

D-Sub Connector PC Pins

152-5209-E, 152-5215-E, 152-5225-E, 152-5237-E, 152-5250-E,
152-5309-E, 152-5315-E, 152-5325-E, 152-5337-E, 152-5350-E

DIMENSIONS: mm (in.)



ELECTRICAL SPECIFICATIONS

Current rating:	5AWG cable
Wire size:	20AWG
Working voltage:	500VAC or DC peak
Contact resistance:	500m Ω
Insulation resistance:	10m Ω
Temperature range:	-55°C to 125°C
Materials:	1. shell: steel with 3-5 u" zinc plating over yellow chromate 2. insulators: polyester 30% glass filled gray 3. contacts: copper alloy, gold plated over nickel
Spacing of rows:	2.84mm (.11)

Mouser Stock No.	Type	# contacts	A	B	C	D	E
152-5209-E	Plug	9	1.213	.984	.488	.431	.984
152-5309-E	Recept	9	1.213	.984	.488	.431	.984
152-5215-E	Plug	15	1.543	1.311	.488	.755	1.311
152-5315-E	Recept	15	1.543	1.311	.488	.755	1.311
152-5225-E	Plug	25	2.091	1.850	.488	1.304	1.852
152-5325-E	Recept	25	2.091	1.850	.488	1.304	1.852
152-5237-E	Plug	37	2.736	2.500	.488	1.956	2.500
152-5337-E	Recept	37	2.736	2.500	.488	1.956	2.500
152-5250-E	Plug	50	2.638	2.406	.606	1.739	2.406
152-5350-E	Recept	50	2.638	2.406	.606	1.739	2.406

RoHS Compliant

Date Last Revised: 01-30-08

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301228

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[152-5250-E](#) [152-5350-E](#) [152-5309-E](#) [152-5225-E](#) [152-5315-E](#) [152-5215-E](#) [152-5209-E](#) [152-5337-E](#) [152-5325-E](#)
[152-5237-E](#)