


# HDMI Receptacle, Type C Right Angle SMT

154-10405-E



HDMI Receptacle, Type C Right Angle SMT



Dimensions: mm

SPECIFICATIONS	MATERIALS
Current Rating: 0.5A	Housing: High temp. plastic, Black
Voltage Rating: 40V DC	Shell: Copper Alloy
Contact Resistance: 30m $\Omega$ MAX.	Shell Plating: Nickel underplating Tin 100 plating
Insulation Resistance: 100m $\Omega$ MIN.	Terminal: Copper Alloy
Operating Temperature: 0°C ~ +50°C	Terminal Plating: Tin selective gold
RoHS Compliant	

Date Last Revised: 06/29/12

Available from Mouser Electronics  
1-800-346-6873 / [www.mouser.com](http://www.mouser.com)

KC-301235

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

154-10405-E

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[154-10405-E](#)