





D-Sub Connectors

156-1410, 156-1416, 156-1426, 156-1438



D-Sub Connectors



Dimensions: In.

| Mouser Stock No. | No. of Contacts | Dimensions (In.) | | | |
|------------------|-----------------|------------------|-------|-------|-------|
| | | A | B | C | D |
| 156-1410 | 9 | .666 | .984 | 1.210 | .759 |
| 156-1416 | 15 | .994 | 1.310 | 1.540 | 1.080 |
| 156-1426 | 25 | 1.530 | 1.850 | 2.090 | 1.630 |
| 156-1438 | 37 | 2.180 | 2.500 | 2.730 | 2.270 |

| MATERIALS | |
|------------|---------------------------|
| Shell: | Steel, Zinc or Tin-Plated |
| Insulator: | Glass Filled Nylon |

| SPECIFICATIONS | |
|-----------------------|------------------------|
| Type: | Connector Plug Housing |
| Current Rating: | 5A |
| Dielectric Strength: | 1000V for 1 Minute |
| Insulator Resistance: | 1000MΩ min. @ 500VDC |
| Temperature: | -55°C ~ +105°C |

Date Last Revised: 10-18-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300658

156-1410, 156-1416, 156-1426, 156-1438

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[156-1410](#) [156-1416](#) [156-1438](#) [156-1426](#)