


PCB Unshielded Receptacles

161-2203, 161-2204, 161-2205,
161-2206, 161-2207, 161-2208



KOBICONN

PCB Unshielded Receptacles


161-2203, 161-2204, 161-2205, 161-2206, 161-2207, 161-2208




8 Pin 161-2208 shown




3 Pin
161-2203




4 Pin
161-2204




5 Pin
161-2205




6 Pin
161-2206



7 Pin
161-2207



8 Pin
161-2208



Dimensions: In.

SPECIFICATIONS	
Type:	Unshielded Miniature Circular
Rating:	1A/100VAC max. or 2A/12VDC max.
Insulation Resistance:	50mΩ min. @ 250VDC
Dielectric Strength:	250VAC for 1 Minute
Contact Resistance:	30mΩ max.
Insertion Force:	4.5Kg max.
Withdrawal Force:	0.9Kg ~ 3Kg
E:	Earth (Ground)

Date Last Revised: 5-11-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300690

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-2204](#) [161-2205](#) [161-2203](#) [161-2208](#) [161-2206](#)