





SMD Phone Jack



161-2625-E



SMD Phone Jack



SOLDERING PADS (BOTTOM VIEW)



Dimensions: mm

ELECTRICAL SPECIFICATIONS	
Voltage rating:	16 VDC
Current Rating:	0.3A
Contact resistance:	30mΩ
Insulation resistance:	100MΩ, 500VDC
Voltage rating:	500VAC for 1 min.
RoHS Compliant	

Tolerance	
X.	±0.5
X.X	±0.3
X.XX	±0.15

MECHANICAL SPECIFICATIONS	
Durability:	5000 cycles
Insertion force:	3Kg to 2.0Kg
Extraction force:	2Kg to 2.0Kg
Soldering temperature:	260°C for 5 seconds
Operating temperature:	-25°C to +85°C

PLATING	
Contacts:	silver

Date Last Revised: 10-2-08

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC- 300968

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

161-2625-E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-2625/TR-E](#) [161-2625-E](#)