


3.5mm Jack

161-3334-E

KOBICONN

3.5mm Jack



SPECIFICATIONS

Housing:	Plastic PA
Contacts:	Phosphor bronze gold plated
Contact Resistance:	50mΩ
Insertion Force:	0.3 KG - 2.0KG
Extraction Force:	0.3 KG - 2.0KG
Operation Temp:	-25°C to +80°C (±2)
Insulation Resistance:	<100MΩ by 500V DC
Voltage:	Withstand 500V AC
Life Time:	5,000 Cycles
Rated Voltage & Current:	DC 16V, 20mA-30mA

Tolerance

±0.5:	X
±0.3:	XX
±0.15:	XXX

Date Last Revised: 03/14/07

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-300976

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

161-3334-E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-3334/TR-E](#) [161-3334-E](#)