






# PC Mount Phono Jacks

161-4213, 161-4216, 161-4217



PC Mount Phono Jacks

Dimensions: In.



## SPECIFICATIONS

<b>Type:</b>	PC mount phono
<b>Impedance:</b>	50mΩ
<b>Initial insertion:</b>	12 lbs (max) w/ $\varnothing$ .128 $\pm$ .0002 pin
<b>Retention:</b>	3oz (min) w/ $\varnothing$ .1235 $\pm$ .0002 after sizing 3 times w/ $\varnothing$ .128 $\pm$ .0002 pin
<b>Temperature rating:</b>	200°C
<b>Shell plating:</b>	161-4213 & 161-4216 nickel, 161-4217 gold
<b>Contact:</b>	tin plated brass
<b>Insulator:</b>	phenolic
<b>Insulator color:</b>	brown(161-4213, 161-4217), black(161-4216)
<b>Washer:</b>	Linen
<b>Insulation Resistance:</b>	100M $\Omega$ (Min.) @ DC500V
<b>Voltage Breakdown:</b>	AC 500V (Minute)
<b>Contact Resistance:</b>	30m $\Omega$ (Max.)

Date Last Revised: 4-19-05

Available from Mouser Electronics  
1-800-346-6873  
www.mouser.com

KC-300366

161-4213, 161-4216, 161-4217

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-4213](#) [161-4216](#) [161-4217](#)