



Cable Assemblies



172-2012-EX, 172-2024-EX, 172-2048-EX, 172-2150-EX

Cable Assemblies

172-2012-EX, 172-2024-EX, 172-2048-EX, 172-2150-EX



Dimensions

Part No.	A		B	
	(In.)	mm	(In.)	mm
172-2012	8.10	205.74	12	304.80
172-2024	20.10	510.54	24	609.60
172-2048	44.10	1120.14	48	1219.20
172-2150	68.10	1729.24	72	1828.80
RoHS Compliant				

Dimensions: mm (In.)

RG58C/U SPECIFICATIONS

Conductor:	Tinned copper wire
Insulation:	PE
Jacket:	PVC black
Jacket diameter:	5.0 mm
Capacitance:	98.7 pF for 1 minute @ 1KHz
Dielectric strength	500V for 1 minute

BNC MALE SPECIFICATIONS

Pin:	Brass, silver
Boot:	PVC, black
Insulator:	Delrim, white
Gasket:	Rubber, red
Spring:	S<-5, nickel
Body:	Brass, nickel plated
Shell:	Brass, nickel plated

Date Last Revised: 8-21-06

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-301043

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[172-2048-EX](#) [172-2150-EX](#) [172-2012-EX](#) [172-2024-EX](#)