



Cable Assemblies

172-2012, 172-2024, 172-2048, 172-2150



Cable Assemblies



Part No.	A		B	
	(In.)	mm	(In.)	mm
172-2012	8.10	205.74	12	304.80
172-2024	20.10	510.54	24	609.60
172-2048	44.10	1120.14	48	1219.20
172-2150	68.10	1729.24	72	1828.80

Dimensions: mm (In.)

RG58C/U SPECIFICATIONS

Conductor:	Tinned copper wire
Insulation:	PE
Jacket:	PVC black
Jacket diameter:	5.0 mm
Capacitance:	98.7 pF for 1 minute @ 1KHz
Dielectric strength	500V for 1 minute

BNC MALE SPECIFICATIONS

Pin:	Brass, silver
Boot:	PVC, black
Insulator:	Delrim, white
Gasket:	Rubber, red
Spring:	S<-5, nickel
Body:	Brass, nickel plated
Shell:	Brass, nickel plated

Date Last Revised: 1-31-06

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300354

172-2012, 172-2024, 172-2048, 172-2150