

You Are Here: [Home](#) > [Coaxial](#) > [Tools](#) > [HT3](#) > [HT301G](#)

Deluxe Coaxial Crimp Tool with .255", .213", .137", .100", .069", .043" Hex Die

Features

- Center contact and connector ferrule crimp tool for various coaxial center contacts and ferrules
- Removable dies for versatility
- Full cycle ratchet reduces fatigue
- Common hex crimp sizes of .255, .213, .137, .100, .069 and .043



This series features a choice of eight similar crimp tools equipped with specific die sets to perform a wide variety of crimping functions that apply to your needs. The supplied die sets are removable and are interchangeable with other die sets within this series.

Details

L-com Item #
Manufacturer
UPC # (More)
RoHS Status

HT301G
L-com
822335028098
[RoHS Compliant](#)

(More)


Applications

Cable assembly
Cable repair
Cable installation

MODEL NUMBER					 PIN	 SQ. PIN	FOR CRIMPING RG TYPE CABLE
HT301A		.256" 6.5	.213" 5.41		.068" 1.72		59, 62, 140, 210, BELDEN 8279, 55, 58, 141, 142, 223, 303, 400, Fiber Optic.
HT301B	.319" 8.1		.213" 5.41	.187" 4.75			6, 55, 58, 141, 142, 223, 303, 400, 174, Fiber Optic
HT301C	.319" 8.1	.256" 6.5	.213" 5.41		.068" 1.72		6, 59, 62, 140, 210, BELDEN 8279, 55, 58, 141, 142, 223, 303, 400, Fiber Optic
HT301D	.324" 8.3	.256" 6.5	.213" 5.41		.068" 1.72		58, 59, 62, 6, 140, 141, 142, 212, 222, 303, Fiber Optic, BELDEN 8282, 8279, 9231, 9141
HT301G	.255" 6.48	.213" 5.41	.137" 3.50	.100" 2.54	.069" 1.75	.043" 1.1	59, 62, 8X, 140, 210, BELDEN 8279, 55, 58, 141, 174, 223, 303, 400, Fiber Optic.
HT301J	.178" 4.52	.151" 3.84	.128" 3.25	.078" 2.00	.068" 1.72	.042" 1.07	122, 174, 179, 180, 187, 188, 195, Fiber Optic, 178, 316, BELDEN 8218
HT301K	.429" 10.9		.128" 3.25	.100" 2.5			8, 9, 11, 87A, 149, 165, 213, 214, 216, 225, 393, 174, 179, 187, 188, 316, BELDEN 9913
HT230A		.255" 6.48	.213" 5.41	.187" 4.75	.068" 1.72		55, 58, 59, 62, 140, 141, 142, 210, 223, 174, 303, 400, Fiber Optic, BELDEN 8279

REVISIONS			
REV	DESCRIPTION	DATE	APPROVAL
A	INITIAL RELEASE	9/28/12	D.FRISIELLO

HT301G RATCHET CRIMPING TOOL



SPECIFICATION:

* Crimping Range :

	.043" 1.09mm				
	.068" 1.73mm	.100" 2.54mm	.137" 3.48mm	.213" 5.41mm	.255" 6.48mm
Description	For Crimping RG 58,59,62,174 Cable Fiber Optic				

* **Length :** 8.7"(220mm)

* **Weight :** 500g

* Material :

Frame - Middle Carbon Steel .

Crimper- Made Of Off Wax.

* Finished :

Black Oxide Finished With Hardened

* **Replacement die P/N:** HT-3G

NOTES:

COMPONENT SHALL BE PACKAGED PER L-COM SPECIFICATION LSP-010-1.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / - 0 >12 [305] - 60 [1524] = +2 [51] / - 0 >60 [1524] - 120 [3048] = +4 [102] / - 0 >120 [3048] - 300 [7620] = +6 [152] / - 0 >300 [7620] = +5% / - 0% ALL OTHER DIMENSIONAL TOLERANCES: .X = .2 .XX = .02 .XXX = .005	APPROVALS	DATE	L-com® Global Connectivity 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845			
	DRAWN BY D.DESJARDIN	9/28/12				
	CHECKED BY D.FRISIELLO	9/28/12	CATEGORY	TOOLS		
	APPROVED BY D.FRISIELLO	9/28/12	PRODUCT DESCRIPTION			
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		HEX CRIMP TOOL MULTI USE			
PROJECTION 	COLOR VARIATIONS MAY OCCUR		SIZE A	FSCM NO. 43321	DWG. NO. HT301G	REV. A
			SCALE: 1:1		CAD FILE: HT301G.SLDDRW	