





Dimensions in mm unless specified otherwise

*Drill out 3.0mm dia. x
12mm deep where HD1
= 1.0mm or 1.60mm

Part No.	Alternative Part No.	Material	BODY					OLIVE				CAP						
			HD1	T1	TL1	T2	TL2	AF1	HL	HD2	OL	OD1	OD2	HD3	T3	CL	CT	AF2
Non-stock	—	Brass	*1.10	1/8"bspt	8.5	MBx1	6.5	11.1	3.7	1.10	4.2	3.0	1.5	1.10	MBx1	10.0	3.0	11.1
FC-001	XR-077/XF-122	Brass	*1.60	1/8"bspt	8.5	MBx1	6.5	11.1	3.7	1.80	4.7	4.0	2.0	1.60	MBx1	10.0	3.0	11.1
FC-002	XR-074/XF-123	Brass	3.10	1/8"bspt	8.5	MBx1	6.5	11.1	3.7	3.10	5.0	5.0	3.5	3.10	MBx1	10.0	3.0	11.1
FC-004	—	Brass	3.25	1/8"bspt	8.5	MBx1	6.5	11.1	3.7	3.25	5.0	5.0	3.7	3.25	MBx1	10.0	3.0	11.1
FC-005	—	Brass	4.10	1/8"bspt	8.5	M10x1	6.5	12.7	4.7	4.10	5.5	6.0	4.5	4.10	M10x1	12.0	3.5	12.7
XS-251	FC-005-4	Brass	4.60	1/8"bspt	8.5	M10x1	6.5	12.7	4.7	4.60	6.0	7.0	5.0	4.60	M10x1	12.0	3.5	12.7
FC-008	—	Brass	4.85	1/8"bspt	8.5	M10x1	6.5	12.7	4.7	4.85	6.2	7.0	5.3	4.85	M10x1	12.0	3.5	12.7
FC-011	XF-124	Brass	6.10	1/8"bspt	8.5	M10x1	6.5	12.7	4.7	6.10	6.4	8.0	6.5	6.10	M10x1	12.0	3.5	12.7
FC-130	XF-027	303 st/st	*1.10	1/8"bspt	8.5	MBx1	6.5	11.1	3.7	1.10	4.2	3.0	1.5	1.10	MBx1	10.0	3.0	11.1
FC-131	XF-019/XS-096	303 st/st	*1.60	1/8"bspt	8.5	MBx1	6.5	11.1	3.7	1.60	4.7	4.0	2.0	1.60	MBx1	10.0	3.0	11.1
FC-133	XF-020/XQ-091	303 st/st	3.10	1/8"bspt	8.5	MBx1	6.5	11.1	3.7	3.10	5.0	5.0	3.5	3.10	MBx1	10.0	3.0	11.1
FC-134	—	303 st/st	3.25	1/8"bspt	8.5	MBx1	6.5	11.1	3.7	3.25	5.0	5.0	3.7	3.25	MBx1	10.0	3.0	11.1
Non-stock	—	303 st/st	4.10	1/8"bspt	8.5	M10x1	6.5	12.7	4.7	4.10	5.5	6.0	4.5	4.10	M10x1	12.0	3.5	12.7
XS-253	—	303 st/st	4.60	1/8"bspt	8.5	M10x1	6.5	12.7	4.7	4.60	6.0	7.0	5.0	4.60	M10x1	12.0	3.5	12.7
FC-135	—	303 st/st	4.85	1/8"bspt	8.5	M10x1	6.5	12.7	4.7	4.85	6.2	7.0	5.3	4.85	M10x1	12.0	3.5	12.7
FC-136	—	303 st/st	6.10	1/8"bspt	8.5	M10x1	6.5	12.7	4.7	6.10	6.4	8.0	6.5	6.10	M10x1	12.0	3.5	12.7

A	NEW DRAWING	SD	19.11.01	MATERIAL	TOLERANCE:	TITLE		DRAWN	CHECKED	DATE:
B	CHANGE TOL'S & DIMS TO OLIVES & CHAMFERS	SD	25.01.02	See above	X ±0.25mm X.X ±0.10mm X.XX ±0.05mm	1/8" BSPT (Tapered) Compression Fittings		SD		19.11.01
C	INNER NUT & BODY ANGLES CHANGED TO 45°	SD	26.09.02	FINISH: Clean & free of burrs	SCALE: NTS	PART NUMBER: See above		DRAWING NO.		
ISSUE	MODIFICATION	BY/APP.	DATE	THIS DRAWING REMAINS THE PROPERTY OF LAFACILITY LIMITED AND MAY NOT BE REPRODUCED WITHOUT OUR PERMISSION						
			SHEET 1 OF 1 SHEETS							