


EPIC® Pin & Sleeve Connectors

30 Amp: North American Version
CEE Angled Female Panel Mount Receptacle

IP 67



Technical Data

Impact Resistance:	8J
Ambient Temperature:	-25°C to 70°C
Flame Resistance:	
➤Glow Wire Test: Enclosure:	850°C
➤Glow Wire Test: Contact Enclosure:	850°C
➤Self-Extinguishing: Enclosure:	UL94-V2
➤Self-Extinguishing: Contact Carrier:	UL94-V2

Part Numbers

Part Number	Voltage	# of Wires	# of Poles	Ground-Clock Position
471267FX	125	3	1+N+PE	4
471367FX	250	3	2+PE	6
471556FX	480	3	2+PE	7
471867FX	125 / 250	4	2+N+PE	12
471377FX	3Ø250	4	3+PE	9
471577FX	3Ø480	4	3+PE	7
471387FX	3ØY 120 / 208	5	3+N+PE	9
471567FX	3ØY 277 / 480	5	3+N+PE	7