


Product Description



Application

Chromium nickel steel cable gland with metric connecting thread in accordance with EN 50262 with Viton® seal, specially designed for use under tough conditions, e.g. in the pharmaceutical, petrochemical industry (aggressive media) and offshore.

The SKINDICHT® CN-M is stainless and acid resistant.

Note

- suitable counter nut SKINDICHT® SM CrNi M please see chart

Technical Data

Caution

Installation dimensions see T21

Material

Body: Chrome-nickel steel in accordance with DIN,
material no. 1.4305 Seal: FPM O-ring: FPM

Degree of protection

IP68

Range of temperature

-25°C up to +200°C

Article List

Part number	Part designation / size	Clamping range ØF mm	Overall length C mm	Thread length D mm	SW mm	Pieces / VPE
SKINDICHT® CN-M						
52032580	12 x 1,5/1	3,5 - 5	27	10	17	5
52032590	12 x 1,5/2	5 - 6,5	27	10	17	5
52032600	12 x 1,5/3	6,5 - 8	27	10	17	5
52032610	16 x 1,5	8 - 10,5	30	10	18	5
52032620	20 x 1,5	11 - 15	31	10	24	5
52032630	25 x 1,5	16 - 20,5	36	11	30	5
52032640	32 x 1,5	21 - 25,5	41	13	36	5
52032650	40 x 1,5	28,5 - 33	44	13	46	1
52032660	50 x 1,5	37 - 42	48	14	55	1
52032670	63 x 1,5	46 - 52	51	14	70	1
SKINDICHT® SM CrNi M counter nuts						
52032585	12 x 1,5	-	3	3	17	10
52032615	16 x 1,5	-	3	3	19	10
52032625	20 x 1,5	-	3,5	3,5	24	10
52032635	25 x 1,5	-	3,5	3,5	30	10
52032645	32 x 1,5	-	4,5	4,5	36	10
52032655	40 x 1,5	-	4,5	4,5	46	10
52032665	50 x 1,5	-	5,5	5,5	55	10
52032675	63 x 1,5	-	6	6	70	10