

Product Description

90° elbow enables best assembling; Fast assembly; High-tensile; Sealing; Vibration protection



Application range

- In combination with protective conduit
- SILVYN® FPAS
- Applications with strong vibrations
- For applications with limited space

Benefits

- 90° elbow enables best assembling
- Fast assembly
- High-tensile
- Sealing
- Vibration protection

Design

- Metric connection thread
- 90° elbow
- Body
- Upper part with integrated all-round toothing

Approvals

- UL FILENUMBER E308201
- UNDERGROUND

Product features

- In black colour UV-resistant and weather-proofed
- Removeable with a screwdriver

Technical Data

Colour delivered

Black (RAL 9005), UV-resistant Grey (RAL 7001)

Material

PA66 Halogen-free

Protection rating

IP66

Temperature range

-50°C to +135°C

Article List

Part number	Article designation	Suitable for SILVYN® FPAS	Pieces / PU
SILVYN® FPAG 90° M black			
55506485	M12x1,5	10	10
55506495	M16x1,5/1	13	10
55506505	M16x1,5/2	16	10
55506515	M20x1,5/1	16	10
55506525	M20x1,5/2	21	10
55507075	M20x1,5/3	18	10
55506535	M25x1,5	28	10
55506545	M32x1,5	34	10
55507085	M40x1,5	42	1
55506555	M50x1,5/1	42	1
55506565	M50x1,5/2	54	1
55506575	M63x1,5/1	54	1
55507095	M63x1,5/2	67	1
SILVYN® FPAG 90° M grey			
55506480	M12x1,5	10	10
55506490	M16x1,5/1	13	10
55506500	M16x1,5/2	16	10
55506510	M20x1,5/1	16	10
55506520	M20x1,5/2	21	10

55507070	M20x1,5/3	18	10
55506530	M25x1,5	28	10
55506540	M32x1,5	34	10
55507080	M40x1,5	42	1
55506550	M50x1,5/1	42	1
55506560	M50x1,5/2	54	1
55506570	M63x1,5/1	54	1
55507090	M63x1,5/2	67	1

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.