



<b>Ordering number</b>	<b>C11506</b>		
<b>Description</b>	<b>C11506-Brooke-MBH-S</b>		
Family	Brooke-MBH	FWHM	04degrees
Type	Reflector	Efficiency	-
LED	BXRA-C0800/1200/2000	cd/lm	-
Color	Metal	Gerber File	Available
Diameter	45 mm		
Height	19.5 mm		
Style	Round		
Optic Material	-		
Holder Material	-		
Fastening	-		
Status	Ready		



<b>Ordering number</b>	<b>C11507</b>		
<b>Description</b>	<b>C11507-Brooke-MBH-M</b>		
Family	Brooke-MBH	FWHM	02degrees
Type	Reflector	Efficiency	-
LED	BXRA-C0800/1200/2000	cd/lm	-
Color	Metal	Gerber File	Available
Diameter	45 mm		
Height	19.5 mm		
Style	Round		
Optic Material	-		
Holder Material	-		
Fastening	-		
Status	Ready		



<b>Ordering number</b>	<b>C11508</b>		
<b>Description</b>	<b>C11508-Brooke-MBH-W</b>		
Family	Brooke-MBH	FWHM	00degrees
Type	Reflector	Efficiency	-
LED	BXRA-C0800/1200/2000	cd/lm	-
Color	Metal	Gerber File	Available
Diameter	45 mm		
Height	19.5 mm		
Style	Round		
Optic Material	-		
Holder Material	-		
Fastening	-		
Status	Ready		



<b>Ordering number</b>	<b>C11506</b>		
<b>Description</b>	<b>C11506-Brooke-MBH-S</b>		
Family	Brooke-MBH	FWHM	04degrees
Type	Reflector	Efficiency	-
LED	BXRA-C0800/1200/2000	cd/lm	-
Color	Metal	Gerber File	Available
Diameter	45 mm		
Height	19.5 mm		
Style	Round		
Optic Material	-		
Holder Material	-		
Fastening	-		
Status	Ready		

## Brooke-MBH series



<b>Ordering number</b>	<b>C11507</b>		
<b>Description</b>	<b>C11507-Brooke-MBH-W</b>		
Family	Brooke-MBH	FWHM	62degrees
Type	Reflector	Efficiency	-
LED	BXRA-C0800/1200/2000	cd/lm	-
Color	Metal	Gerber File	Available
Diameter	45 mm		
Height	19.5 mm		
Style	Round		
Optic Material	-		
Holder Material	-		
Fastening	-		
Status	Ready		



<b>Ordering number</b>	<b>C11508</b>		
<b>Description</b>	<b>C11508-Brooke-MBH-W</b>		
Family	Brooke-MBH	FWHM	60degrees
Type	Reflector	Efficiency	-
LED	BXRA-C0800/1200/2000	cd/lm	-
Color	Metal	Gerber File	Available
Diameter	45 mm		
Height	19.5 mm		
Style	Round		
Optic Material	-		
Holder Material	-		
Fastening	-		
Status	Ready		



## Brooke-MBH series

Specially designed for BXRA-C0800/1200/2000 series of LEDs.


Reflector material optical grade metal and protective lacquer coated PC (120 degrees of Celcius/24 degrees of Fahrenheit). Allows use of high current and temperature conditions.

D


C

B


A




Isometric view



Bottom view



Front view



Top view

Part No.s:  
 C11506\_Brooke-MBH-S  
 C11507\_Brooke-MBH-M  
 C11508\_Brooke-MBH-W

Material: PC with Metal coating  
 and clear lacquer

This drawing is our property.  
 It can't be reproduced  
 or communicated without  
 our written agreement.



Ledil Oy  
 Tehdaskatu 13  
 FIN-24100 SALO  
 Finland

DRAWING TITLE

Datasheet Brooke-MBH Ref1

DRAWN BY

mav

DATE

27.01.2011

CHECKED BY

tk

DATE

27.01.2011

SIZE

A4

DRAWING NUMBER

REV

1

DESIGNED BY

o1

DATE

01.01.2011

SCALE

1:1

WEIGHT (g)

SHEET

1/1

D

A

4

4

3

3

2

2

1

1