




4890
**UNIDIRECTIONAL, FEMALE-
FEMALE, BSP PARALLEL**

4890

Specifications

maximum working pressure	bar 40	MPa 4,0	psi 580
working temperature	°C (Celsius) From -20 to 180	F (Fahrenheit) From -4 to 356	K (Kelvin) From 253 to 453
shut-off valve	stainless steel 316L		
body	stainless steel 316L		
'O'-rings	Fluoroelastomer FKM (FPM)		
spring	stainless steel 302		



4890
UNIDIRECTIONAL, FEMALE-
FEMALE, BSP PARALLEL
 for metric tubing

4890

Dimensions

convert weight : kg | oz
 convert dimensions : mm | inch

	ØD (mm)	C	F (mm)	L (mm)	 (kg)
4890 10 10	22	G1/8	17,0	50,0	0,000
4890 13 13	22	G1/4	17,0	50,0	0,000
4890 17 17	30	G3/8	22,0	67,0	0,000
4890 21 21	30	G1/2	24,0	71,0	0,000
4890 27 27	35	G3/4	32,0	78,0	0,000
4890 34 34	42	G1	38,0	90,0	0,000