



marathon™
Special Products

Product Data Sheet

133X558

Replace "x" with 1, 2, or 3 for number of poles

Add suffix "CH" for snap-on hinged cover

Power Terminal Block

310 Amps 600 Volts AC/DC

Wire Range

- Line: (1) 350kcmil - #6 AWG
- Load: M10 X 30 Stud

Electrical Ratings

- 310 Amps
- 600V per UL 1059 & CSA 22.2 No.158, class B & C requirements
- SCCR of 10,000 A (default for terminal blocks).
- CU7AL - 75°C connector terminal rating with copper or aluminum wire
- Factory & Field Wiring

Agency Compliance

- UR - UL Recognized Terminal Block, Evaluated to UL 1059, File No.XCFR2.E62806
- CSA - certified to C22.2 No. 158, File No. LR19766 (wire classes B & C only)
- CE compliant to IEC 60947-7-1


Material Information

- Insulator base:
 - Thermoplastic
 - Flammability rating of insulator base UL94V0
 - Insulator base temperature rating: -40°C to 125°C (UL RTI)
- Connector: aluminum, tin plated
- Terminal set screws: aluminum, tin plated
- Studs: brass, tin plated
- Nuts: brass, nicel plated
- Connector mounting screws: steel, zinc plated
- RoHS compliant


A Regal Brand

REGAL

Termination Specifications

Line Side	Wire Size (CU Stranded)	Torque	Wires / Terminal	Wire Class (UL) ¹
	350 - 300 kcmil	31.1 N·m (275 lbf·in)	1	B, C
	250 - 2	31.1 N·m (275 lbf·in)	1	B, C, G, H, I (DLO)
	4 - 6	31.1 N·m (275 lbf·in)	1	B, C

- Aluminum wire range: 350kcmil - #6 AWG
- Wire strip length: 1.0 in. (25mm)
- Terminal screw drive: 5/16 in. hex

Load Side	Termination Type	Torque	Stud Length (mm/in)	Maximum Lug/Bar Width
	Listed lugs on M10 studs	21.7 N·m (192 lbf·in)	1.18" (30mm)	1.55" (40mm)

- For use with conductors prepared with listed connectors such as single hole compression/crimp lugs or listed ring, fork or spade terminals.
- Conductor size, ampacity, temperature rating and type are dictated by the ratings of the listed lugs utilized and applicable code requirements.

¹ For information on copper stranded wire classes please reference:
<http://www.marathonsp.com/CatalogPDFs/Flexible-Stranded-Wire.pdf>

Installation & Accessories

- Mounting (Panel):
 - For use with #10 fastener.
 - Torque mounting fastener to 25-30 lbf·in (2.8 - 3.4 N·m).
- Covers:
 - Snap-on hinged covers available upon request
 - Catalog Number: CH133x (replace "x" with number of poles)
 - Covers are black thermoplastic
 - Accessory covers are not intended to provide insulation for electrical spacings.
- Marker Strip: white vinyl strip with mounting screws available.
- Printing options available, consult customer service for specifications.

Drawing

