

Double Row Terminal Blocks

400 Series

600 Volts AC/DC (Class C)



Specifications:

- Base, General Purpose Phenolic, 150°C (UL RTI)
- Closed Back Design
- Screws, #10-32 Binder Head, Phil-Slot, Steel
- Terminals, Plated Brass
- 1-12 Poles
- 11/16" Centers
- Wire Range With Wire Binding Screw
#10 - #22 AWG – 30 Amps
- Wire Range With Sems Pressure Screw #10 - #22 AWG
Stranded Copper Wire Only, 30 Amps
- Will Accommodate Lugs for Wire Sizes #6 - #16 AWG, 65 Amps
- UL Recognized File No. XCFR2.E62806
- CSA Certified File No. LR19766
- **CE**
- RoHS Compliant

MSP Catalog #	# of poles	Dimensions	
		A	B
401	1	1.81	1.38
402	2	2.50	2.06
403	3	3.19	2.75
404	4	3.88	3.44
405	5	4.56	4.12
406	6	5.25	4.81
407	7	5.94	5.50
408	8	6.62	6.19
409	9	7.31	6.88
410	10	8.00	7.56
411	11	8.68	8.25
412	12	9.37	8.94

mm=dim X 25.4

For electronic drawings or 2D/3D CAD data, submit request at www.marathonsp.com/drawings.html

Hardware Options:

(Hardware options may affect ratings - consult Customer Service)

CATALOG # MSP	KULKA	PRODUCT DESCRIPTION	PAGE REFERENCE
F1	KT67	Full Quick Connect (0° Flat)	See page 105
F2	KT68	Full Quick Connect (45° Bend)	See page 105
F3	KT69	Full Quick Connect (90° Bend)	See page 105
HF1	KT64	Half Quick Connect (0° Flat)	See page 105
HF2	KT65	Half Quick Connect (45° Bend)	See page 105
HF3	KT66	Half Quick Connect (90° Bend)	See page 105
LL 400	J 603	Line to Line Jumper	See page 107
SPSE		SEMS Pressure Saddle Screw	Consult C/S
PSB		Phil-Slot Brass Screw	Consult C/S

Quick Connects: .032" x .250"

See pages 104-115 for terminal block accessories

