

5186 Max. 130 W
SWITCH MODE POWER SUPPLY

- Max. 130 W output power
- Universal input voltage
- 3-pin IEC 320 mains connector
- Compliance with relevant worldwide safety standards



Technical specifications	12 V	24 V
	Input voltage	90-264VAC 47-63 Hz
Output voltage	12 VDC ± 2.5 %	24 VDC ± 2.5 %
Max. output power cont.	130W	
Load current	10.83A	5.41A
Load regulation	5%	
Line regulation	3%	
Switch frequency	50kHz	
Overshoot	5%	
Undershoot	5%	
Inrush current	20A for 115VAC or 40A for 230 VAC	
Hold up time	5m S	
No load input current	0.17 for 90 VAC	
Temperature range	0-70°C	
Temperature coefficient	+/- 0.04% Celcius	
Ripple (max)	120mV p-p	240mV p-p
Efficiency	85%	
Current limiting	0-10.83A	0-5.41A
Overvoltage protection	13.44-15.84VDC	26,88-31,68VDC
Protection	Input surge , OVP, UVP, OLP	
Insulation class	Class II	
Insulation voltage	PS 4666VDC, PG 2120VDC, SG 500VDC	
Electrical safety	EN/UL 60950	
EMC standard, Emission	EN 55022, CLASS B	
EMC standard, Immunity	EN 61000-6-1, EN 61000-6-3	
Reliability, at 70°C , 80W	100 000hrs MTBF Min.	
Mains connection	3 PIN IEC 320	
Outout terminals	5 PIN DIN w. 4FT 16AWG	
Indication	LED INDICATION	
IP grade	IP44	
Dimensions	196x88x50	
Weight	960g	

14062006

www.mascot.no
sales@mascot.no
Main Office
 PO Box 177
 N-1601 FREDRIKSTAD
 NORWAY
 Phone: +47 69 36 43 00
 Fax: +47 69 36 43 01

Mascot UK
 Box 2090, Salisbury
 Wiltshire SP2 2BH
 UK
 +44 1722 504 853
 +44 845 299 1210

Mascot DE-AT-CH-BENELUX
 Hirschbergstr. 28/7
 D-74838 LIMBACH
 GERMANY
 +49 6287 95140
 +49 6287 95141
 Tettnanger Str. 52
 D-88239 WANGEN
 GERMANY
 +49 7528 951677
 +49 7528 951678

Mascot France
 38 rue Leo Lagrange
 94270 Le Kremlin Bicêtre
 FRANCE
 +33 1 46 58 71 85
 +33 1 46 58 71 85