




order number : 1267

Receptacle

external fixing, one cable entry from top
 16A4P 9H230V wall mounted receptacle TA
 IP44



Zeichnung	Amp.	16			32		
		3	4	5	3	4	5
1 MB 205	Pole						
Maße in mm	a	91	91	91	102	102	102
	b	73	79	87	89	89	94
	c	86	93	99	108	108	114
	d	55	55	56,4	62	62	62
	e	62	68	76	77,5	77,5	84
	f	5,3	5,3	5,3	5,3	5,3	5,3
	g	8	8	9	10	10	10
	h	132	132	132	153	153	153
	M	20	25	25	25	25	32
	Leitung bis mm Ø	13	18	18	18	18	25
	Klemmen für Leiterquerschnitt von bis mm ²	1,5	1,5	1,5	2,5	2,5	2,5
		-4	-4	-4	-10	-10	-10

Article-group : 1037

voltages : 230V

rated current : 16A

pole : 4 pole

IP protection types : IP44

position of ground contact : 9h

packing unit : 0010

pilot contact (63A-125A) : without pilot-contact

contact carriers : standard

contact technique : screw contact

weight : 220 g

PART NUMBERS

	V	110V	230V	400V	500V	>50-500V	
		50,60	50,60	50,60	50,60	100-300	300-500
colour	amp.						
	amp.	16 A	32 A				
	3	1177	1178				
	4		1267	1268	1269		
	3	1368	1369				
	4		1372	1373	1374		