


# MALE PCB PINS

## PRINTED CIRCUIT PINS

### 3120

3120-X-00-XX-00-00-08-0

Swage mount in 0,86 hole




| Basic Part Number | Pin Length A |
|-------------------|--------------|
| 3120-1            | 5,21         |
| 3120-2            | 6,35         |

### 3122⇨3153

31XX-X-00-XX-00-00-08-0

Swage mount in 1,09 hole



| Basic Part Number | Pin Length A |
|-------------------|--------------|
| 3153-X            | 4,57         |
| 3141-X            | 5,84         |
| 3122-X            | 7,11         |
| 3149-X            | 9,65         |
| 3123-X            | 14,73        |
| 3140-X            | 19,81        |
| 3124-X            | 22,35        |


  

| - X - | Board Thickness | Length V |
|-------|-----------------|----------|
| 1     | 0,79            | 1,3      |
| 2     | 1,57            | 2,08     |

### 3101⇨3106

310X-X-00-XX-00-00-08-0

Swage mount in 1,09 hole



| Basic Part Number | Pin Length A |
|-------------------|--------------|
| 3101-X            | 3,81         |
| 3102-X            | 4,78         |
| 3103-X            | 7,62         |
| 3104-X            | 12,7         |
| 3105-X            | 19,05        |
| 3106-X            | 25,40        |


  

| - X - | Board Thickness | Length V |
|-------|-----------------|----------|
| 1     | 0,79            | 1,30     |
| 2     | 1,57            | 2,08     |
| 3     | 2,39            | 2,87     |

### 3221⇨3223

322X-0-00-XX-00-00-08-0

Swage mount in 1,09 hole



| Basic Part Number | Pin Length A |
|-------------------|--------------|
| 3221-X            | 2,54         |
| 3222-X            | 3,81         |
| 3223-X            | 7,62         |


  

| - X - | Board Thickness | Length V |
|-------|-----------------|----------|
| 1     | 0,79            | 1,30     |
| 2     | 1,57            | 2,08     |
| 3     | 2,39            | 2,87     |

### 3125/3126

312X-X-00-XX-00-00-08-0

Swage mount in 1,09 hole



| Basic Part Number | Pin Length S |
|-------------------|--------------|
| 3125-X            | 4,32         |
| 3126-X            | 10,67        |


  

| - X - | Board Thickness | Length V |
|-------|-----------------|----------|
| 1     | 0,79            | 1,30     |
| 2     | 1,57            | 2,08     |
| 3     | 2,39            | 2,87     |

### 0995

0995-0-00-XX-00-00-03-0


Press-fit in 1,45 mounting hole



### 4526

4526-0-00-XX-00-00-03-0

Press-fit in 1,02 mounting hole



#### SPECIFICATIONS:

**Pin Material:** Brass Alloy 360, 1/2 Hard  
( Except swage pins which are annealed )

**Dimensions:** Millimeters

**Tolerances On:** Lengths:  $\pm 0,13$   
Diameters:  $\pm 0,051$   
Angles:  $\pm 2^\circ$



ORDER CODE: XXXX - X - 0X - XX - 00 - 00 - XX - 0

BASIC PART #

SPECIFY PIN FINISH:

- 01 5,08μm TIN/LEAD OVER NICKEL
- ◆ 80 5,08μm TIN OVER NICKEL (RoHS)
- ◆ 15 0,25μm GOLD OVER NICKEL (RoHS)
- ◆ 21 0,51μm GOLD OVER NICKEL (RoHS)
- ◆ 34 1,27μm GOLD OVER NICKEL (RoHS)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com