



PART NO.	LENGTH	REF. OVERALL LENGTH
847271002	1.5M (4' 11.06")	1.55M (5 FT 1 1/8 IN.)
847271001	2.0M (6' 6.74")	2.05M (6 FT 8 13/16 IN.)
847271003	3.0M (9' 10.10")	3.05M (10 FT 3/16 IN.)
847271004	5.0M (16' 4.85")	5.05M (16 FT 6 7/8 IN.)
847271005	0.15M (0' 5.91")	0.20M (0 FT 8 IN.)
847271905	0.27M (0' 10.63")	0.32M (0 FT 12 3/4 IN.)





BAYONET STYLE
LOCKING INTERFACE

P1	
RED	1
WHT	2
GRN	3
BLK	4
DRAIN	
	SHIELD

WIRING DIAGRAM

NOTES: UNLESS OTHERWISE SPECIFIED.

1. MATERIAL: SEE TABLE.
2. FINISHES: SEE TABLE.
3. PRODUCT SPEC: PS-84727-002
4. PACKAGING: SEALED POLY BAG.
5. MATES WITH: USB TYPE-A RECEPTACLES.
6. ASSEMBLY IS RoHS COMPLIANT.



6	1	WRAP LABEL	PLASTIC FILM	BLACK/YELLOW
5	1	GASKET SEAL	NITRILE	BLACK
4	1	OVER MOLDING	PVC	BLACK
3	1	HOLDER	POLYESTER	BLACK
2	1	COUPLING RING	POLYESTER	BLACK
1	1	USB TYPE-A PLUG SHIELDED PIGTAIL	BRASS/PLASTIC	
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH

ADDED P/N
EC NO: WNA2011-0167
DR: WILKINSON 2010/10/19
CHKD: L. HARTMANN 2010/10/26
APPR: J. MURPHY 2010/12/14

QUALITY
SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± .005	± .0005
3 PLACES	± .01	± .001
2 PLACES	± .03	± .003
1 PLACE	± .075	± .003
ANGULAR ± 2 °		

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
IN/MM

DRAWN BY	DATE
S. GILBERT	06-30-04
CHECKED BY	DATE
G. ROBERTSON	10-05-04
APPROVED BY	DATE
J. MURPHY	2009/12/15

MATERIAL NO. SEE CHART

SCALE
1:1

DESIGN UNITS
INCH

THIRD ANGLE
PROJECTION

PLUG, USB TYPE-A,
SHIELDED, PIGTAIL C1C

MOLEX INCORPORATED

DOCUMENT NO. SD-84727-001

SHEET NO.
1 OF 1