

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200800089](#)
Status: **Active**
Overview: Brad Ultra-Lock Connection System
Description: Ultra-Lock (M12) In-Line Splitter Cordset, 4 Poles, 3-Female (Straight) to 4-Male (90°), 0.34mm² TPE Cable, 0.30m Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837

General

Product Family Industrial Tees and Splitters
 Series [120080](#)
 IP Rating IP68
 Overview [Brad Ultra-Lock Connection System](#)
 Product Name Ultra-Lock (M12)
 Type Splitter - In-line
 UPC 78678887302

Physical

Color - Cable Jacket Yellow
 Drop Connector Ultra-Lock (M12)
 Drop Gender Male
 Keyway Single
 LED Indicator No
 Left Trunk Connector Ultra-Lock (M12)
 Left Trunk Gender Female
 Leg 1 Length 0.30m
 Leg 2 Length 0.30m
 Material - Cable Jacket TPE
 Material - Connector Body TPE
 Material - Coupling Nut Nickel-plated Brass
 Poles 3 Female/4 Male
 Right Trunk Connector Ultra-Lock (M12)
 Right Trunk Gender Female
 Temperature Range - Operating -30°C TO +80°C

Electrical

Current - Maximum per Contact 4.0A
 Voltage - Maximum 250V AC/DC

Material Info

Engineering Number WW4A31K05M003

Reference - Drawing Numbers

Sales Drawing SD-120080-029



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[120080 Series](#)