

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [130153-0141](#)  
**Status:** **Active**  
**Overview:** Ground Fault Circuit Interrupter (GFCI) Products  
**Description:** Super-Safeway® In-Line Industrial GFCI, Portable, Single Phase, Automatic Reset, Outlet Box, NEMA 5-20 Double Duplex with Flip Lids, 15A, 120V, 0.61m (2.0') Cord Length

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

[Product Literature \(PDF\)](#)

**Agency Certification**

UL E66308

**General**

Product Family	Power Distribution
Series	<a href="#">130153</a>
Enclosure Rating	NEMA 4
GFCI Reset	Automatic
Mounting Style	Portable
Open Neutral Relay	Yes
Overview	<a href="#">Ground Fault Circuit Interrupter (GFCI) Products</a>
Product Literature Order No	987650-7737, 987651-0452
Product Name	Super-Safeway™
Receptacle Type	Duplex
Type	GFCI Industrial Duty, Single Phase
UPC	78678888305
Woodhead	Yes

**Physical**

Cord Diameter	10.67mm (.420")
Cord Grip Body Size	Internal Double C-Clamp
Cord Length	0.61m (2.0')
Feed-Thru	Yes
Flip Lid	Yes
Material - Housing	Nylon
Net Weight	999.990/kg
Number of Receptacles	2
Packaging Type	Bag

**Electrical**

Cord Type	12/3 SJEOOW
Current - Maximum per Contact	20A
GFCI	Yes-In-line
Ground Continuity Monitor	No
NEMA Configuration	NEMA 5-20
Voltage - Maximum	N/A

**Material Info**

Old Part Number 20053W-2A



*image - Reference only*

**EU RoHS**

**China RoHS**

**Compliance Status**

**Not Reviewed**

**REACH SVHC**

**Not Reviewed**

**Low-Halogen Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[130153Series](#)