

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130153-0147](#)
Status: **Active**
Overview: Ground Fault Circuit Interrupter (GFCI) Products
Description: Safeway® In-Line Commercial GFCI, Permanent Mount, Single Phase, Manual Reset, NEMA L6-20, 20A, 120V, 1.83m (6.0') Cord Length

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)
[Product Literature \(PDF\)](#)

Agency Certification

CSA LR6837

General

Product Family	Power Distribution
Series	130153
Enclosure Rating	NEMA 4
GFCI Reset	Manual
Mounting Style	Portable
Open Neutral Relay	Yes
Overview	Ground Fault Circuit Interrupter (GFCI) Products
Product Literature Order No	987650-7737, 987651-0452
Product Name	Safeway®
Receptacle Type	N/A
Type	GFCI Commercial Duty, Single Phase
UPC	78678837417
Woodhead	Yes

Physical

Cord Diameter	10.92mm (.430")
Cord Grip Body Size	Internal Double C-Clamp
Cord Length	1.83m (6.0')
Feed-Thru	Yes
Flip Lid	No
Material - Housing	Nylon
Net Weight	136.070/kg
Number of Receptacles	1
Packaging Type	Bag

Electrical

Cord Type	12/3 SJTW
Current - Maximum per Contact	20A
GFCI	Yes-In-line
Ground Continuity Monitor	No
NEMA Configuration	NEMA L6-20
Voltage - Maximum	120V

Material Info

Old Part Number 20054-6



EU RoHS

China RoHS

Compliance Status

Not Reviewed

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[130153Series](#)