

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0015496601](#)
Status: **Obsolete**
Description: 2.54mm (.100") Pitch MX-50™ Center Polarization Receptacle, 60 Circuits

Documents:
[Drawing \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family Ribbon Cable / Wire Trap Connectors
 Series [70625](#)
 Comments Center Polarization
 Component Type Housing
 Glow-Wire Compliant No
 Product Name MX-50™

Physical

Circuits (Loaded) 60
 Entry Angle 90° Angle
 Flammability 94V-0
 Lock to Mating Part Yes
 Number of Rows 2
 PCB Retention None
 Packaging Type Tube
 Pitch - Mating Interface 2.54mm (.100")
 Polarized to Mating Part Yes
 Stackable No
 Surface Mount Compatible (SMC) N/A
 Temperature Range - Operating -40°C to +105°C
 Wire Insulation Diameter 1.14mm (.045") max.
 Wire Size AWG 26, 28
 Wire/Cable Type Ribbon Cable

Electrical

Current - Maximum per Contact 1A
 Voltage - Maximum 125V

Material Info

Old Part Number 70625-1044P

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[70625Series](#)

Mates With
 .025" Square or Round Pins, [70246](#) Straight Header, [70247](#) Right Angle Header