

	10	9	8	7	6	5	4	3	2	19070				
	LOOSE PIECE		TAPE MOUNTED		SPECIFICATIONS									
	MATERIAL NUMBER	ALTERNATE NUMBER	MATERIAL NUMBER	ALTERNATE NUMBER	HOUSING COLOR	STUD SIZE	"S" ±.005/(0.13)	"W" MAX.	"C" MIN.	"L" MAX.	"ID" MIN.	STOCK THICKNESS REFERENCE	"H" ±.020/-.051	
F	I90700005	AA-220-02X	I90700006	AA-220-02XT	RED	2	.094/(2.39)	.235/(6.00)	.157/(3.99)	.709/(18.01)	.062/(1.57)	.028/(0.71)	.980/(24.89)	F
	I90700007	AA-220-04X	I90700008	AA-220-04XT	RED	4	.119/(3.02)							
	I90700009	AA-220-06X	I90700010	AA-220-06XT	RED	6	.146/(3.71)							
	I90700011	AA-221-06X	I90700012	AA-221-06XT	RED	6	.146/(3.71)	.322/(8.18)	.270/(6.86)	.866/(22.00)	.062/(1.57)	.028/(0.71)		E
	I90700013	AA-221-08X	I90700014	AA-221-08XT	RED	8	.173/(4.39)							
	I90700015	AA-221-10X	I90700017	AA-221-10XT	RED	10	.198/(5.03)							
	I90700019	AA-221-209X	I90700020	AA-221-209XT	RED	M5	.209/(5.18)	.477/(12.11)	.386/(9.80)	1.060/(26.92)	.062/(1.57)	.028/(0.71)		D
E	I90700021	AA-222-10X	I90700022	AA-222-10T	RED	10	.198/(5.03)							
	I90700023	AA-222-14X	I90700024	AA-222-14XT	RED	14	.265/(6.73)							
	190700608	AA-222-14X-BK	I90700601	AA-222-14XT-BK	BLACK	14	.265/(6.73)							
	I90700026	AA-222-56X	I90700027	AA-222-56XT	RED	5/16"	.328/(8.33)	.544/(13.82)	.552/(14.02)	1.259/(31.98)	.055/(1.40)	.031/(0.79)	1.172/(29.77)	D
	190700609	AA-222-56X-BK	190700611	AA-222-56XT-BK	BLACK	5/16"	.328/(8.33)							
	I90700029	AA-226-10X	I90700030	AA-226-10XT	RED	10	.198/(5.03)							
D	I90700031	AA-226-14X	I90700032	AA-226-14XT	RED	14	.265/(6.73)	.264/(6.70)	.240/(6.10)	.807/(20.50)	.062/(1.57)	.028/(0.71)	.980/(24.89)	
	I90700036	AA-226-56X	I90700037	AA-226-56XT	RED	5/16"	.328/(8.33)							
	I90700033	AA-226-38X	I90700035	AA-226-38XT	RED	3/8"	.390/(9.91)							
	I90700038	AA-232-04X	I90700039	AA-232-04XT	RED	4	.119/(3.02)	.283/(7.20)	.240/(6.10)	.816/(20.73)	.062/(1.57)	.028/(0.71)		
	I90700040	AA-232-06X	I90700042	AA-232-06XT	RED	6	.146/(3.71)							
	I90700044	AA-232-08X	I90700045	AA-232-08XT	RED	8	.173/(4.39)							
	I90700051	AA-233-10X	I90700052	AA-233-10XT	RED	10	.198/(5.03)	.283/(7.20)	.240/(6.10)	.816/(20.73)	.062/(1.57)	.028/(0.71)		
	190700612	AA-233-10X-BK	190700614	AA-233-10XT-BK	BLACK	10	.198/(5.03)							

SALES DRAWING

NOTE(S):
1. MATERIAL: COPPER
PLATING: ELECTROPLATE TIN
2. DELETED
3. INSULATION: MOLDED PVC, SEE CHART FOR COLOR
4. MWID=MAXIMUM WIRE INSULATION DIA.
5. ALL DIMENSIONS IN INCHES (MM).
6. PARTS ARE ROHS COMPLIANT.

ADD NEW PART #S BK HSG
EC NO: IFC2015-2037
IDRWINGR0JAS01 2015/05/28
CHKD: JMACNEIL
APPR: JMACNEIL 2016/03/24
C3

DESCRIPTION
REV

QUALITY SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	±---	±---
3 PLACES	±---	±---
2 PLACES	±---	±---
1 PLACE	±---	±---
ANGULAR ±---°		

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
IN/MM

DRAWN BY DATE
DMYRICK 2005/7/22

CHECKED BY DATE
HBEITZEL 2005/7/22

APPROVED BY DATE
RDEROSS 2005/7/22

MATERIAL NO.
SEE CHART

SCALE

DESIGN UNITS
INCH

THIRD ANGLE PROJECTION

RING TONGUE TERMINAL
INSULKRIMP, 200-SERIES
22-18 AWG

MOLEX INCORPORATED

DOCUMENT NO.
SD-19070-003

SHEET NO.
1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION