

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [35711-0610](#)
Status: **Active**
Description: 2.79mm Slip-In Receptacle, Quick Disconnect, 0.50mm Tab Thickness, Wire Range 20-22 AWG (0.52-0.33mm²), Post-Tin Plated

Documents:

Drawing (PDF)	Packaging Specification PK-35711-001 (PDF)
Product Specification PS-35112-001 (PDF)	Packaging Specification PK-35711-003 (PDF)
Product Specification PS-35711-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Quick Disconnects
Series	35711
Crimp Quality Equipment	Yes
Product Name	Slip-On
Type	Quick Disconnect
UPC	800754782173

Physical

Barrel Type	Open
Gender	Female
Glow-Wire Compliant	No
Insulation	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.226/g
Orientation	Straight
Packaging Type	Reel
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Polarized to Mating Part	No
Tab Thickness	0.51mm
Tab Width	2.79mm
Temperature Range - Operating	-40°C to +120°C
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.50-2.40mm max.
Wire Size AWG	20, 22
Wire Size mm ²	0.33 - 0.52


Electrical

Voltage - Maximum	Per Wire Specification
-------------------	------------------------

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-35711-001, PK-35711-003
Product Specification	PS-35112-001, PS-35711-001
Sales Drawing	SD-35711-060



EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[35711Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[35711-0610](#)