

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0395285146](#)
Status: **Obsolete**
Description: 5.00mm (.197") Pitch Eurostyle™ Horizontal PCB Dual Level Header, with Standard Imprinting, Open Ends, Green Housing, 46 Circuits

Documents:
[Drawing \(PDF\)](#)

General

Product Family	Terminal Blocks
Series	39528
Application	Wire-to-Board
Comments	with Standard Imprinting
Component Type	PCB Header
Product Name	ESE, Eurostyle™ Pluggable
Type	Euro Block


Physical

Circuits (Loaded)	46
Entry Angle	N/A
Lock to Mating Part	Yes
Number of Rows	2
Orientation	Horizontal
PC Tail Length	5.00mm (.197")
PCB Thickness - Recommended	3.05mm (.120")
Panel Mount	No
Pitch - Mating Interface	5.00mm (.197")
Pitch - Termination Interface	5.00mm (.197")
Polarized to Mating Part	Yes
Shrouded	Open Ends
Stackable	Yes
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-40°C to +105°C
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	15A
Voltage - Maximum	300V

Material Info



EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[39528Series](#)

Mates With

39520 Horizontal Plug, 39523 Vertical Plug, Most 5.00mm (.197") Pitch Industry Standard Plugs