

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0710783120](#)
Status: **Obsolete**
Description: 1.27mm (.050") Pitch PC Card Header, Dual Port Right Angle, Top Mount, Through Hole

Documents:
[Drawing \(PDF\)](#)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Memory Card Sockets
Series	71078
Component Type	Header/Socket (Host)
Product Name	PC Card
Style	Guide and Holder
Type	I, II, III

Physical

Card Detection Switch	N/A
Circuits (Loaded)	68+68
Durability (mating cycles max)	10,000
Ejector Button	No
Ejector Button Side	N/A
Entry Angle	90° Angle (Side Entry)
Flammability	94V-0
Keying to Mating Part	Yes
PC Tail Length	1.95mm (.077")
PCB Mounting Side	Normal
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm (.063"), 2.50mm (.098")
Packaging Type	Tray
Pitch - Mating Interface	1.27mm (.050")
Ports	2
Temperature Range - Operating	-20°C to +60°C

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	100V AC
Voltage Key	5.0V

Material Info

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[71078Series](#)

Use With
[87510 Ejector](#), [87510 Guide Rails](#)