


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0984381003](#)
Status: **Active**
Description: 5.00mm Pitch NSCC/SICMA Female Wire-to-Board Housing, for 2.80mm Tab, with Bridges, Dual Row, 6 Circuits, Gray

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Application Specification AS-98438-001-001 \(PDF\)](#)

General	
Product Family	Crimp Housings
Series	98438
Application	Power, Wire-to-Board
Comments	For current designation please refer to FCI Sicma terminal specification for 2.80mm terminals.
Product Name	NSCC
UPC	822350104319
Physical	
Circuits (maximum)	6
Color - Resin	Black, Natural
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	5.162/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	98438-1001
Reference - Drawing Numbers	
Application Specification	AS-98438-001-001
Sales Drawing	SD-98438-001



Series image - Reference only

EU ELV	
Compliant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Contained Per - ED/61/2018 (27 June 2018)	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
[98438](#) Series

Mates With
[98898](#) UCC2 Terminals

Use With
[98898](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION