

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130109-0017](#)
Status: **Active**
Description: Pro-Yellow® Nylon 100W Hand Lamp with Switch, Molded Grips and Hide Away Guard, Cord Type 18/3 SJTW, Cord Length 6.10m (20.0')

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

UL E59049

General

Product Family Portable Lighting
Series [130109](#)
NEMA Configuration NEMA 5-15
Outlet None
Product Literature Order No 987650-8053
Product Name Pro-Yellow®
Type Hand Lamps
UPC 78678850114
Woodhead Yes

Physical

Cord Length - Primary 6.10m (20.0')
Cord Length - Secondary N/A
Depth N/A
Duty General
Guard Included No
Guard Type N/A
Height N/A
Length N/A
Material - Guard Polypropylene
Mounting Style Hand Held
Packaging Type Carton
Socket Construction N/A

Electrical

Bulb Type Incandescent
Cord Type - Primary 18/3 SJTW
Lamp Type A21
Lamp Wattage - Maximum 100W
Lumens 1000
On/Off Switch Yes
Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Old Part Number WT3C-20



image - Reference only

Series

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[130109Series](#)