


Pin Header Micro Match 1,27 mm

Series

373



Rated current	1,5 A
Rated voltage	230 V _{RMS} / V _{DC}
Withstand voltage	1000 V _{RMS} for one minute
Material contact	Phosphor bronze
Material insulator	High temp. thermoplast UL94V-0
Operating temperature	-40°C to +105°C
Max. processing temper.	260°C for 10 seconds


pitch	1,27
termination	
max. pincount	026

All dimensions in mm.



Variation

Compatible with industries standard.


PCB Layout



1



2



no. of contacts	see figure left	see figure left	available in variation
n	A	B	
004	7,20	2,54	1
006	9,74	5,08	1
008	12,28	7,62	1
010	14,82	10,16	1
012	17,36	12,70	1
014	19,90	15,24	1
016	22,44	17,78	1
018	24,98	20,32	1
020	27,52	22,86	1
022	30,06	25,40	1
024	32,60	27,94	1
026	35,14	30,48	1
004	7,10	2,54	2
006	9,64	5,08	2
008	12,18	7,62	2
010	14,72	10,16	2
012	17,26	12,70	2
014	19,80	15,24	2
016	22,34	17,78	2
018	24,88	20,32	2
020	27,42	22,86	2
022	29,96	25,40	2
024	32,50	27,94	2
026	35,04	30,48	2

Plating:
T = Sn

Packaging:
T = Tube

Variation (1,2)

No. of contacts

Plating contact

Packaging



www.mpe-connector.de

Order code:

373-2-222-0-T-KT0

Mating series	369	374
see page	4-12	4-13

Product
group
3