

Resonators > CERALOCK (kHz) > Part Number

How to check EU RoHS Compliant of Our Products is [here](#).

Product Lifecycle Stage	in Production
Recommended Rank	Preferred














Specification

Global Part Number	CSBFB455KJ58-R1
Previous Part Number	CSBF455J-TC01
Nominal Frequency	455.0kHz
Initial Tolerance	±0.5%
Temp. Stability	±0.3%
Temperature Range	-20 to +80°C
Wash	Available
Ultrasonic Wash	Available
Built-in Load Capacitance	
Use	For consumer electronics

Minimum Quantity

180mm Paper Tape	
180mm Embossed Tape	
330mm Paper Tape	
330mm Embossed Tape	3000
Bulk Case	
Bulk(Bag)	
Ammo Pack	
320Reel	
Magazine	
Box	

Details

- ?  [Part Numbering](#)
- ?  [Appearance \(430 to 519kHz\)](#)
- ?  [Dimensions \(430 to 519kHz\)](#)
- ?  [Features and Applications](#)
- ?  [Temperature Characteristics](#)
- ?  [Basic Oscillation Circuit](#)
- ?  [Standard Land Pattern Dimensions \(430 to 519kHz\)](#)
- ?  [Notice \(storage and operating condition\)](#)
- ?  [Notice \(rating\)](#)
- ?  [Notice \(soldering and mounting\) \(430 to 519kHz\)](#)
- ?  [Notice \(handling\)](#)
- ?  [Packaging \(430 to 519kHz\)](#)
- ?  [Minimum Quantity\[Supplementation\]](#)

Please approve our product specifications or to transact the approval sheet for product specifications before ordering. Please read rating and !Cautions first. Product specifications in this catalog are as of January 2008.

All products and company names herein are trademarks or registered trademarks of their respective owners.