

Resonators > CERALOCK (kHz) > Part Number

How to check EU RoHS Compliant of Our Products is [here](#).

Product Lifecycle Stage	in Production
Recommended Rank	Preferred

Specification

Global Part Number	CSBLA500KEC8-B0
Previous Part Number	CSB500E
Nominal Frequency	500.0kHz
Initial Tolerance	
Temp. Stability	±0.3%
Temperature Range	-20 to +80°C
Wash	Not Available
Ultrasonic Wash	Not Available
Built-in Load Capacitance	
Use	For consumer electronics

Minimum Quantity

180mm Paper Tape	
180mm Embossed Tape	
330mm Paper Tape	
330mm Embossed Tape	
Bulk Case	
Bulk(Bag)	500
Ammo Pack	
320Reel	
Magazine	
Box	

Details

- ?  [Part Numbering](#)
- ?  [Appearance/Dimensions_\(430_to_509kHz\)](#)
- ?  [Appearance/Dimensions_\(430_to_509kHz\)](#)
- ?  [Features_and_Applications](#)
- ?  [Temperature_Characteristics](#)
- ?  [Basic_Oscillation_Circuit](#)
- ?  [Notice_\(storage_and_operating_condition\)](#)
- ?  [Notice_\(rating\)](#)
- ?  [Notice_\(soldering_and_mounting\)](#)
- ?  [Notice_\(handling\)](#)
- ?  [Minimum_Quantity\[Supplementation\]](#)

Please approve our product specifications or to transact the approval sheet for product specifications before ordering. Please read rating and !Cautions first.
Product specifications in this catalog are as of January 2008.

All products and company names herein are trademarks or registered trademarks of their respective owners.