




Visit Murata's Website at www.murata.com

RPE Radial Lead Ceramic Capacitors



These monolithic ceramic capacitors have industry standard sizes and an epoxy coating meeting UL94V-0. Leads are tinned copper clad steel wire. Additional values, voltages, temperature coefficients, tolerances and markings available, as well as additional lead spacing and tape and reel option available as custom order. Call for price and delivery.

Dimensions (mm)				
Type	H	L	T	LS
RPE110	3.1	3.5	2.5	2.5
RPE113	3.5	5.1	3.2	5.1
RPE114	10.2	10.2	4.0	5.1
RPE117	12.7	12.7	5.1	10.2
RPE121	6.4	5.1	3.2	2.5
RPE122	6.4	5.1	3.2	5.1
RPE123	7.0	7.6	3.2	5.1
RPE131	3.5	5.1	3.2	2.5
RPE132	5.1	3.5	3.2	5.1

Stock No.	Mfr.'s Type	VDC	Value (pF)	Tol. %	Temp. Coeff.	EACH	
						1-99	100-249
711-1500	RPE110COG100C050V	50	10	.25 pF	COG	.41	.31
711-1502	RPE110COG180J050V	50	18	5	COG	.48	.34
711-1504	RPE110COG220J050V	50	22	5	COG	.22	.16
711-1506	RPE110COG270J050V	50	27	5	COG	.49	.35
711-1508	RPE110COG330J050V	50	33	5	COG	.51	.34
711-1510	RPE110COG390J050V	50	39	5	COG	.28	.21
711-1512	RPE110COG470J050V	50	47	5	COG	.55	.37
711-1514	RPE110COG101J050V	50	100	5	COG	.51	.35
711-1516	RPE110COG181J050V	50	180	5	COG	.59	.36
711-1518	RPE110COG221J050V	50	220	5	COG	.65	.46
711-1520	RPE110COG271J050V	50	270	5	COG	.61	.40
711-1522	RPE110COG331J050V	50	330	5	COG	.58	.37
711-1524	RPE110COG391J050V	50	390	5	COG	.56	.37
711-1526	RPE110COG471J050V	50	470	5	COG	.28	.17
711-1528	RPE110COG102J050V	50	1000	5	COG	.64	.43
711-1530	RPE110X7R471K050V	50	470	10	X7R	.27	.21
711-1532	RPE110X7R102K050V	50	1000	10	X7R	.53	.35
711-1534	RPE110X7R103K050V	50	10000	10	X7R	.57	.36

Stock No.	Mfr.'s Type	VDC	Value (pF)	Tol. %	Temp. Coeff.	EACH	
						1-99	100-249
711-1536	RPE110X7R223K050V	50	22000	10	X7R	.61	.40
711-1538	RPE110Z5U102M050V	50	1000	20	Z5U	.25	.20
711-1540	RPE110Z5U103M050V	50	10000	20	Z5U	.24	.17
711-1544	RPE113X7R474K050V	50	470000	10	X7R	1.25	1.03
711-1546	RPE113X7R105K050V	50	1000000	10	X7R	2.15	1.60
711-1548	RPE113Z5U105M050V	50	1000000	20	Z5U	2.58	1.92
711-1552	RPE114X7R155K050V	50	1500000	10	X7R	1.75	1.50
711-1554	RPE114X7R185K050V	50	1800000	10	X7R	6.54	4.74
711-1558	RPE114Z5U225M050V	50	2200000	20	Z5U	2.97	2.11
711-1560	RPE114Z5U335M050V	50	3300000	20	Z5U	6.19	4.59
711-1564	RPE117X7R225K050V	50	2200000	10	X7R	8.65	6.50
711-1566	RPE117Z5U475M050V	50	4700000	20	Z5U	6.41	4.76
711-1568	RPE121COG151J050V	50	150	5	COG	.39	.29
711-1570	RPE121COG102J050V	50	1000	5	COG	.47	.35
711-1572	RPE121X7R103K050V	50	10000	10	X7R	.18	.12
711-1574	RPE121X7R473K050V	50	47000	10	X7R	.22	.16
711-1576	RPE121X7R104K050V	50	100000	10	X7R	.25	.17
711-1578	RPE121Z5U103M050V	50	10000	20	Z5U	.24	.17
711-1580	RPE121Z5U104M050V	50	100000	20	Z5U	.32	.19
711-1582	RPE121Z5U224M050V	50	220000	20	Z5U	.32	.22
711-1584	RPE121Z5U334M050V	50	330000	20	Z5U	.39	.24
711-1594	RPE122COG102J050V	50	1000	5	COG	.71	.49
711-1596	RPE122X7R471K050V	50	470	10	X7R	.37	.27
711-1598	RPE122X7R472K050V	50	4700	10	X7R	.62	.39
711-1600	RPE122X7R103K050V	50	10000	10	X7R	.64	.41
711-1602	RPE122X7R473K050V	50	47000	10	X7R	.63	.41
711-1604	RPE122X7R104K050V	50	100000	10	X7R	.83	.55
711-1606	RPE122Z5U103M050V	50	10000	20	Z5U	.67	.40
711-1608	RPE122Z5U104M050V	50	100000	20	Z5U	.40	.28
711-1612	RPE122Z5U334M050V	50	330000	20	Z5U	.38	.25
711-1614	RPE123Z5U474M050V	50	470000	20	Z5U	.50	.32
711-1616	RPE123Z5U105M050V	50	1000000	20	Z5U	.36	.26
711-1746	RPE131X7R102K050V	50	1000	10	X7R	.17	.10
711-1750	RPE131X7R103K050V	50	10000	10	X7R	.15	.11
711-1754	RPE131X7R104K050V	50	100000	10	X7R	.19	.13
711-1756	RPE131Z5U103M050V	50	10000	20	Z5U	.20	.18
711-1758	RPE131Z5U104M050V	50	100000	20	Z5U	.18	.13
711-1764	RPE132X7R103K050V	50	10000	20	X7R	.27	.20
711-1768	RPE132X7R104K050V	50	100000	20	X7R	.26	.17
711-1772	RPE132Z5U104M050V	50	100000	20	Z5U	.15	.11
711-1650	RPE110COG100C100V	100	10	.25 pF	COG	.66	.38
711-1652	RPE110COG120J100V	100	12	5	COG	.30	.23
711-1654	RPE110COG150J100V	100	15	5	COG	.35	.26
711-1656	RPE110COG180J100V	100	18	5	COG	.50	.37
711-1658	RPE110COG220J100V	100	22	5	COG	.47	.35
711-1660	RPE110COG270J100V	100	27	5	COG	.56	.42
711-1662	RPE110COG330J100V	100	33	5	COG	.64	.41
711-1664	RPE110COG390J100V	100	39	5	COG	.51	.38
711-1666	RPE110COG470J100V	100	47	5	COG	.32	.24
711-1668	RPE110COG101J100V	100	100	5	COG	.21	.15
711-1670	RPE110COG121J100V	100	120	5	COG	.35	.26
711-1672	RPE110COG151J100V	100	150	5	COG	.32	.24
711-1674	RPE110COG181J100V	100	180	5	COG	.32	.24
711-1676	RPE110COG221J100V	100	220	5	COG	.28	.20
711-1678	RPE110COG331J100V	100	330	5	COG	.60	.44
711-1680	RPE110COG391J100V	100	390	5	COG	.72	.51
711-1682	RPE110COG471J100V	100	470	5	COG	.66	.47
711-1684	RPE110X7R331K100V	100	330	10	X7R	.32	.24
711-1688	RPE110X7R102K100V	100	1000	10	X7R	.51	.36
711-1690	RPE110X7R222K100V	100	2200	10	X7R	.54	.40
711-1692	RPE110X7R332K100V	100	3300	10	X7R	.33	.25
711-1694	RPE110X7R472K100V	100	4700	10	X7R	.43	.32
711-1696	RPE110X7R103K100V	100	10000	10	X7R	.24	.18
711-1543	RPE113COG103J100V	100	10000	5	COG	2.41	1.79
711-1700	RPE113X7R224K100V	100	220000	10	X7R	1.32	.99
711-1706	RPE114X7R105K100V	100	1000000	10	X7R	3.22	2.32
711-1708	RPE114Z5U105M100V	100	1000000	20	Z5U	3.86	2.86
711-1710	RPE117Z5U225M100V	100	2200000	20	Z5U	6.02	5.35
711-1714	RPE121COG152J100V	100	1500	5	COG	.63	.47
711-1716	RPE121X7R103K100V	100	10000	10	X7R	.14	.10
711-1718	RPE121X7R104K100V	100	100000	10	X7R	.54	.34
711-1720	RPE121Z5U104M100V	100	100000	20	Z5U	.47	.31
711-1726	RPE122COG101J100V	100	100	5	COG	.71	.51
711-1730	RPE122COG102J100V	100	1000	5	COG	.99	.72
711-1738	RPE122X7R223K100V	100	22000	10	X7R	.47	.35
711-1740	RPE122X7R104K100V	100	100000	10	X7R	1.12	.80
711-1744	RPE122Z5U104M100V	100	100000	20	Z5U	.49	.44
711-1752	RPE131X7R103K100V	100	10000	10	X7R	.30	.23

10