


DESCRIPTION: 9 POS MICRO-D FEMALE (ASSEMBLED) TO BLUNT CUT



- 1. P1. CONNECTOR: NORCOMP MICRO D 9S, ASSEMBLED HOOD W/THUMBSCREWS
- 2. P2. BLUNT CUT END
- 3. WIRE: 28AWG [7X36] x9C +ALUMINUM FOIL W/ BRAID 65%, UL2464+CSA, COLOR BLACK
- 4. PINOUT:

P1	P2
1	BLACK
2	BROWN
3	RED
4	ORANGE
5	YELLOW
6	GREEN
7	BLUE
8	VIOLET
9	GRAY
SHELL	DRAIN

CCA-009-YYR152

I = INCHES
F = FEET
M = METERS

LENGTH

EXAMPLES:

CCA-009-I18R152 = 18 INCHES

CCA-009-F03R152 = 3 FEET

CCA-009-M01R152 = 1 METER

PACKAGED: 1 PER BAG

RoHS COMPLIANT

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: P. JENKINS		DATE: 01-18-12		
		CHECKED:		DATE:		
	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	SCALE: NTS		SHEET 1 OF 1		REV 0
		NorComp				