


# Desoldering Tips

for MFR-DSX, -DSI, -SDX and -SDI Systems



| Part No.          | Description             | Ø A            | Ø B            |
|-------------------|-------------------------|----------------|----------------|
| D <b>F</b> P-CN2  | Desolder Tip            | 0.67mm (.026") | 0.67mm (.026") |
| D <b>F</b> P-CN3  | Desolder Tip            | 0.79mm (.031") | 2.05mm (.080") |
| D <b>F</b> P-CN4  | Desolder Tip            | 1.05mm (.041") | 2.30mm (.090") |
| D <b>F</b> P-CN5  | Desolder Tip            | 1.31mm (.052") | 2.65mm (.104") |
| D <b>F</b> P-CN6  | Desolder Tip            | 1.55mm (.061") | 2.85mm (.112") |
| D <b>F</b> P-CN7  | Desolder Tip            | 2.44mm (.096") | 3.65mm (.143") |
| D <b>F</b> P-CNL3 | Desolder Tip Long Reach | 0.79mm (.031") | 2.05mm (.080") |
| D <b>F</b> P-CNL4 | Desolder Tip Long Reach | 1.05mm (.041") | 2.30mm (.090") |
| D <b>F</b> P-CNL5 | Desolder Tip Long Reach | 1.31mm (.052") | 2.65mm (.104") |

The second digit denotes substrate material (damage tolerance). **F**= FR4 / Glass Fiber, for most standard applications. Also available in C Series, **C** = Ceramic.

# Soldering Tips

for MFR-PST and PS-800E Systems with MFR-CA2 and PS-CA2 coils

**EASY ACCESS SOLDERING TIPS** *for longer reach touch up applications*

|  |                                                              |  |                                                               |
|--|--------------------------------------------------------------|--|---------------------------------------------------------------|
|  | <b>SFV-CN05A</b><br>Conical Solder Tip<br>0.5mm (.02")       |  | <b>SFV-CH18A</b><br>Fine Solder Tip<br>1.8mm (.07")           |
|  | <b>SFV-CNL10A</b><br>Conical Long Solder Tip<br>1.0mm (.04") |  | <b>SFV-CH15A</b><br>Chisel Solder Tip<br>1.5mm (.06")         |
|  | <b>SFV-CH50A</b><br>Chisel Solder Tip<br>5.0mm (.197")       |  | <b>SFV-CNL03A</b><br>Conical Long Solder Tip<br>0.3mm (.01")  |
|  | <b>SFV-CH25A</b><br>Chisel Solder Tip<br>2.5mm (.10")        |  | <b>SFV-CNB04A</b><br>Conical Bent Solder Tip<br>0.4mm (.016") |
|  | <b>SFV-CH10A</b><br>Chisel Solder Tip<br>1.0mm (.04")        |  | <b>SFV-DRH430A</b><br>Drag Solder Tip<br>Hoof, 3.0mm (.12")   |
|  | <b>SFV-DRH420A</b><br>Hoof Solder Tip 45°<br>2.0mm (.08")    |  | <b>SFV-DRK45A</b><br>Knife Solder Tip<br>4.5mm (.177")        |
|  |                                                              |  | <b>SFV-DRK30A</b><br>Knife Solder Tip<br>3.0mm (.12")         |

**SOLDERING TIPS** *for heavy duty applications*

|  |                                                          |  |                                                              |
|--|----------------------------------------------------------|--|--------------------------------------------------------------|
|  | <b>SFV-CH10</b><br>Chisel Solder Tip<br>30° 1.0mm (.04") |  | <b>SFV-CNL10</b><br>Conical Long Solder Tip<br>1.0mm (.04")  |
|  | <b>SFV-CH20</b><br>Chisel Solder Tip<br>2.0mm (.08")     |  | <b>SFV-CNL14</b><br>Conical Long Solder Tip<br>1.4mm (.056") |
|  | <b>SFV-CH25</b><br>Chisel Solder Tip<br>2.5mm (.10")     |  | <b>SFV-DRH20</b><br>Conical Bevel Solder Tip<br>2.0mm (.08") |